

VOLLWEG
BIPLAQUE
FULL WAVE

HOCHVAKUUM
A VIDE POUSSE
HIGH VACUUM

Heizspannung	V_f	= 4,0 V
Tension de chauffage		
Filament voltage		
Heizstrom	I_f	ca.
Courant de chauffage		= env. 0,4 A
Filament current		appr.
Anodenwechselspannung	$V_{a \max}$	= 2×250 V
Tension plaque c.a.		
A.C. anode voltage		
Gleichgerichteter Strom	$I_{a \max}$	= 30 mA
Courant redressé		
Rectified current		
Max. Länge	l	= 93 mm
Longueur max.		
Overall length		
Grösster Durchmesser	d	= 47 mm
Diamètre max.		
Max. diameter		
Sockel		= A 35
Culot		
Base		
Sockelschaltung		= S III
Connexion du culot		
Base connection		

$V_g(V)$

PHILIPS

1801

500

400

300

200

100

$V_{eff} = 2 \times 250V$

$V_{eff} = 2 \times 200V$

$V_{eff} = 2 \times 150V$

$I_a(mA)$

0

4

8

12

16

20

24

28

32

