



1EP2

1EP2

OSCILLOGRAPH TUBE

ELECTROSTATIC FOCUS

ELECTROSTATIC DEFLECTION


The 1EP2 is the same as the 1EP1 except for the following items:

General:

Phosphor (For Curves, see front of this Section) P2
 Fluorescence Greenish-Yellow
 Phosphorescence Greenish-Yellow
 Persistence Long

In general, operation of the 1EP2 at an ultor voltage less than 750 volts is not recommended.

AVERAGE CHARACTERISTICS



TUBE DIVISION

RADIO CORPORATION OF AMERICA, HARRISON, NEW JERSEY

92CM-9189


IEP2



IEP2

AVERAGE CHARACTERISTICS

$E_f = 6.3$ VOLTS
ULTOR VOLTS = 1000
GRID-N^o 3 VOLTS ADJUSTED FOR FOCUS.



TUBE DIVISION

RADIO CORPORATION OF AMERICA, HARRISON, NEW JERSEY

92CM-9298