



3WP2

OSCILLOGRAPH TUBE

ELECTROSTATIC FOCUS

ELECTROSTATIC DEFLECTION

The 3WP2 is the same as the 3WP1 except for the following items:

General:

Phosphor (For Curves, see front of this Section)	P2
Fluorescence	Greenish-Yellow
Phosphorescence	Greenish-Yellow
Persistence	Long

Line width and drive values for the 3WP2 are the same as those shown for type 3WP1 under the heading SPECIAL PERFORMANCE DATA and are based upon operation at brightness values calculated from 3WP1 performance.

3WP11

OSCILLOGRAPH TUBE

ELECTROSTATIC FOCUS

ELECTROSTATIC DEFLECTION

The 3WP11 is the same as the 3WP1 except for the following items:

General:

Phosphor (For Curves, see front of this Section)	P11
Fluorescence	Blue
Phosphorescence	Blue
Persistence	Short

Line width and drive values for the 3WP11 are the same as those shown for type 3WP1 under the heading SPECIAL PERFORMANCE DATA and are based upon operation at brightness values calculated from 3WP1 performance.

