


VACUUM TUBE PRODUCTS

VTP IONIZATION GAUGE TUBE TYPE 6578

The VTP 6578 Ionization Gauge Tube is the ultimate in reliability and accuracy for measuring vacuum in large metal systems. The inherent design incorporating the use of pure metals, accurate electrode positioning and freedom from connecting tube restrictions allow a precise measurement of low pressures. By utilizing a design with the grid surrounding the collector, the absolute minimum of errors in gas pressure are obtained, inasmuch as the collector is physically small and few gas molecules are released by collector ion bombardment. The VTP 6578 is constructed with three separately connected filaments providing the maximum in gauge reliability when used on large systems and where a shutdown for gauge tube replacement is costly. Provision is also made for outgassing the grid by direct heating by applying a voltage to the two end connections brought out to separate base pins. Grid out gassing may be done while the tube is in operation, if desired.



SCALE FULL SIZE

NOTE: The collector of the VTP 6578 does not require outgassing due to its small size and the radiation heating from the grid outgas operation.

GENERAL CHARACTERISTICS

Filaments	Note: Use filaments individually for maximum life.		Three.				
Filament Voltage (Single Filament)		5.0 Max. Volts					
Filament Current		6.0 Max. Amps					
Grid Voltage (Referenced to Filament)		500 Max. Volts					
Grid Voltage (Referenced to Flange)		500 Max. Volts					
Grid Current (Emission Current)		15 Max. Ma					
Grid Voltage (Pin 3 to Pin 5)		5 Max. Volts					
Grid Current (Pin 3 through Pin 5 circuit)		4 1/4 Max. Amps					
Collector Voltage (Referenced to Filament)		500 Max. Volts					
Collector Voltage (Referenced to Flange)		500 Max. Volts					
Collector Current	Varies directly with gas pressure and directly with grid current						
When filament is hot do not exceed following pressures							
Pressure Maximum (Corrosive Gasses or Nitrogen)		5 Microns					
Pressure Maximum (Noble gasses or Hydrogen)		2 Atmospheres					
NOTE: It is not necessary to remove the VTP 6578 when pressure testing metal systems for leaks.							
Case		Ceramic	RETMA A7.14				
Basing			RETMA 7EH				
Pin No.	1	2	3	4	5	6	7
Element	F1F2	F1	G	C	G	F3	F2F3
Mounting (Mechanical)	6 equally spaced					13/64" holes on 2 1/4" hole circle	
Mounting Position						Any	
Maximum Flange Temperature						180°C	


TYPICAL OPERATION

Filament Voltage	Single Filament.	Approx. 3.0 Volts
(Adjust to provide 5 ma Emission to Grid)		
Filament Current	(when obtaining emission from 1 filament)	Approx. 4.0 Amps
Grid Voltage (Use voltage regulated supply)		150 Volts
Grid Current (Adjust filament voltage to obtain this value)		5 Ma
Collector Voltage		-30 Volts
Collector Current	(Depends on gas and on gas pressure) 60 Microamps/micron for Dry Air	
Grid Outgassing Operation	Apply 5 volts at approx 4 amps between pins 3 and 5 until gas pressure measured is stable.	

VACUUM TUBE PRODUCTS, 506 SOUTH CLEVELAND STREET, OCEANSIDE, CALIFORNIA
 Feb. 1955 TELEPHONE: SARatoga 2-6567

IONIZATION GAUGE TUBE TYPE 6578

A gasket groove $1\frac{1}{2}$ " I.D. x $1\frac{7}{8}$ " O.D. x .100" deep is provided in the $2\frac{5}{8}$ " diameter flange to accommodate AN6227B-28 O-Rings. Six equally spaced $13/64$ " holes on a $2\frac{1}{4}$ " hole circle are provided to facilitate clamping to a flange on the vacuum system. A clearance of $1\frac{1}{4}$ " diameter by $2\frac{5}{8}$ " deep is required to avoid damage to tube elements when installing the VTP 6578.






Base—Ceramic RETMA A7-14

BASING PEH

Typical curves with $E_g = +150$ $E_p = -30$

Note: Do not exceed 10 ma grid current to obtain maximum filament life.

5 ma I_g is normal operating current.



VACUUM TUBE PRODUCTS, 506 SOUTH CLEVELAND STREET, OCEANSIDE, CALIFORNIA

Feb. 1955

TELEPHONE: SARatoga 2-6567