

CHARACTERISTICS

GENERAL DATA

Focusing Method	Self Focusing (Electrostatic)
Deflecting Method	Magnetic
Deflection Angles (approx.)	
Vertical	68 Degrees
Horizontal	85 Degrees
Diagonal	90 Degrees
Phosphor	P4
Fluorescence	White
Persistence	Short to Medium
Faceplate	Gray Filter Glass
Light Transmittance (approx.)	80 Percent

ELECTRICAL DATA

Heater Voltage	6.3 Volts
Heater Current (approx.)	0.6 Ampere
Direct Interelectrode Capacitances (approx.)	
Cathode to All Other Electrodes	5 μ f
Grid No. 1 to All Other Electrodes	6 μ f

MECHANICAL DATA

Minimum Useful Screen Dimensions	7-3/16 x 5 3/8 Inches
Bulb Contact (Recessed Small Cavity Cap)	J1-21
Base (Small Shell Duodecal 5-Pin)	B5-57
Basing	12S

RATINGS

MAXIMUM RATINGS (Absolute Maximum Values)

Anode Voltage	22,000 Volts dc
Grid No. 2 (and Grid No. 4) Voltage	550 Volts dc
Grid No. 1 Voltage	
Negative Bias Value	155 Volts dc
Negative Peak Value	220 Volts
Positive Bias Value	0 Volts dc
Positive Peak Value	2 Volts
Peak Heater-Cathode Voltage	
Heater Negative with Respect to Cathode	
During Warm-up Period not to Exceed	
15 Seconds	450 Volts
After Equipment Warm-up Period	200 Volts
Heater Positive with Respect to Cathode	200 Volts

TYPICAL OPERATING CONDITIONS

Anode Voltage	16,000 Volts dc
Grid No. 2 (and Grid No. 4) Voltage	300 Volts dc
Grid No. 1 Voltage Required for Cutoff ¹	-28 to -72 Volts dc

CIRCUIT VALUES



Grid No. 1 Circuit Resistance	1.5 Megohms Max.
-------------------------------	------------------

NOTE:

1. Visual extinction of raster.

QUICK REFERENCE DATA

Receiver Check Tube
8" Rectangular, All Glass
Self Focusing (Electrostatic)
No Ion Trap
Magnetic Deflection
Gray Filter Glass



SYLVANIA ELECTRIC
PRODUCTS INC.


TELEVISION PICTURE TUBE
DIVISION

SENECA FALLS, NEW YORK

Prepared and Released By The
TECHNICAL PUBLICATIONS SECTION
EMPORIUM, PENNSYLVANIA

APRIL 1956

PAGE 1 OF 2

**DIAGRAM NOTES:**

1. Reference line is determined by the plane C-C' of the reference line gauge (JETEC No. 116) when the gauge is resting on the glass cone.
2. Anode contact aligns with vacant pin position No. 6 ± 30 degrees.

WARNING:

X-ray radiation shielding may be necessary to protect against possible danger of personal injury from prolonged exposure at close range if this tube is operated at higher than the manufacturer's Maximum Rated Anode Voltage or 16,000 volts, whichever is less.