


F4053 CARCINOTRON

The F4053 "O" type carcinotron is a backward wave oscillator delivering an output power of 15 mW (minimum) to 300 mW over the range 7 to 12.4 GHz.

Amplitude modulation can be achieved by anode voltage variation. Frequency modulation is obtained by varying the line voltage. The frequency is independent of the load up to a VSWR of 3 : 1.

An integral permanent magnet insures focusing, forced air cooling insures operation in a wide temperature range.

This "O" type carcinotron, which features excellent signal to noise ratio is particularly suitable for wide frequency sweep wobbled generator, wide dispersion spectrum analyser, radar panoramic receiver, frequency agile radar (master and local oscillator).



GENERAL CHARACTERISTICS

Electrical (1)

	min.	max.	
Heater voltage	6.3		V
Heater current	0.75	1.80	A
Grid voltage	-100	-	V
Anode voltage (2)	-	170	V
Anode current	-1	+2	mA
Line voltage at 7 GHz	200	-	V
Line voltage at 12.4 GHz	-	1500	V
Line current	-	25	mA
- Line frequency modulation			
Modulation coefficient at 7 GHz	-	13	MHz/V
Modulation coefficient at 12.4 GHz	2	-	MHz/V
- Anode frequency modulation			
Modulation coefficient at 7 GHz	1	-	MHz/V
Modulation coefficient at 12.4 GHz	-	2.5	MHz/V
- Anode amplitude modulation			
Anode voltage variation for an output power variation of 6 dB - at 7 GHz	-	80	V
Anode voltage variation for an output power variation of 6 dB - at 12.4 GHz	15	-	V
- Power variation			
in the range 7 to 12.4 GHz	-	10	dB
in any 0.2 GHz bandwidth	-	1	dB
Grid voltage for cut-off	-100	-	V
- Interelectrode capacitances			
Anode to all other electrodes	-	30	pF
Line to all other electrodes	-	30	pF
Signal to noise ratio between 1 and 10 MHz	40	-	dB

(1) All voltages are referred to the cathode.

(2) Anode or accelerator. Line or cathode may be connected to ground, both are isolated from the focusing device.



Mechanical

Operating position	any
RF connections	50 Ω N type UG 21/U
Weight	2.7 kg
Focusing	permanent magnet
Power supply connections	see drawing

ABSOLUTE RATINGS (non simultaneous values)

	min.	max.			min.	max.	
Heater voltage	6.1	6.5	V	Anode voltage	-	200	V
Heater surge current	-	3.5	A	Anode current	-1	+3	mA
Warm-up time	-	2	mn	Line voltage	-	1600	V
Grid voltage	-125	-	V	Line current	-	30	mA

Cooling

	min.	max.	
Temperature at the measurement point	-	100	$^{\circ}\text{C}$
Air flow	-	10	dm^3/s
Air pressure	-	2.5	millibar
Flow direction	(1)	-	

Environmental conditions

	min.	max.	
Vibrations from 10 to 50 Hz	-	1	mm
Acceleration at 50 Hz	-	1	g
Shocks - acceleration	-	15	g
- duration	-	11	ms
Ambient temperature			
- during operation	-40	+100	$^{\circ}\text{C}$
- during storage	-50	+110	$^{\circ}\text{C}$

TYPICAL OPERATION

Heater voltage	6.3	V	Anode voltage	130	V
Heater current	1.15	A	Anode current	0.01	mA
Frequency	12.4	GHz	Grid voltage	0	V
Line voltage	1310	V	Output power	100	mW
Line current	13.5	mA			

OPERATING INSTRUCTIONS

Application of voltages

Voltages should be applied in the following order : Heater, Grid, Line, Anode.
They should be removed in the reverse order from start up.

Supply

The supply should feature the following security devices :

Warm-up timing,

Power supply protection against arcing or short circuit which may occur in the tube,

Protection against applying voltages before starting air flow,

A safety device should prevent anode voltage from exceeding line voltage, even in case of modulation. If grid and anode power supplies present high internal resistance, a 50 k Ω resistance should be connected in parallel.


Permanent magnet

The tube should be kept away from all magnetic materials, at least 10 cm, and 15 cm away from field generating devices.


(1) T point indicated on drawing



Characteristic curves




Supply diagram





THOMSON-CSF
GROUPEMENT TUBES ELECTRONIQUES

OUTLINE DRAWING



CONNECTIONS	
Heater	Brown
Cathode	Yellow
Anode	Blue
Wehnelt	Green

Dimensions in mm.

