

ELECTRONIC TUBE REFERENCE

18533

Specialized - Radiation Counter electronic tube

CONSOLIDATED TECHNICAL DATA

1 SECTION

CONSTRUCTION

GEIGERMULLERCOUNTER

Halogen-quenched Geiger-Müller radiation counter.

GENERAL CHARACTERISTICS

BASE DESIGNATION	—	BASE PINS	—
NOMINAL HEATER	— / —	PARALLEL HEATER	— / —
HEATING	Indirect	SERIES OPERATION	Not specified
CATHODE ARRANGEMENT	Separate cathodes	SECTION CONSTRUCTION	Similar

SECTION RATINGS

SECTION1 GeigerMullerCounter
No fixed ratings recorded.

SOURCE OPERATING CONDITIONS

[SOURCE PDF](#)

1999 Philips 0-D

Published test conditions and operating points. Values on this page are preserved as reported by this source.

1999 PHILIPS 0-D

Section 1 · GeigerMullerCounter

CHARACTERISTICS		
PARAMETER	PUBLISHED VALUE	CONDITION / NOTE
Starting Voltage	350 V	Maximum starting voltage; minimum 335 V
Operating Voltage	400 V	Minimum operating voltage

TUBE TINKER

An independent reference for electronic tubes, vacuum tubes,
and their source documents.

[Catalog](#) [Tube types](#) [Full books](#) [Blog](#) [Feedback & corrections](#)

© 2026 Tube Tinker